

Rack Safety Plus, 3 U, 400 V AC, 63 A, CEE

KATALOGNUMMER

21270-063



The nVent SCHROFF Rack Safety Plus unit is a 19" power distribution unit used to supply AC mains power to electrical or electronic devices as a central power switch. In addition it is equipped with an emergency stop function.

FUNKTIONER

19", 4 U Power Distribution Unit with Emergency Stop function

Supplies AC mains power to electrical or electronic devices as a central power switch

230 / 400 V 3-phase, 63 A mains input with mains circuit breaker

AC outputs with different connector types, switched by ON/OFF switch

Permanent AC Outputs (Service)

All outputs are protected by circuit breakers

The emergency stop function meets the requirements of EN 60947-5-1 and EN 60204-1 and is vandalism-proof

An additional external emergency stop push button can be connected to the system

PRODUKTEGENSKABER

Product Type: Power Distributor

Accessory Type: Power distribution accessories

Circuit Breaker Cover: Yes

EMC Filter: No

Function: Emergency Stop

Indgangsspænding AC: 400V

Inrush Current Limiter: No

Antal faser: 3

Rack Height: 4U

Residual Current Device: Yes

Stiktype: CEE; IEC C13

Surge Arrester: No

Works With: Varistar; Varistar CP; Novastar

YDERLIGERE PRODUKTOPLYSNINGER

For exact configuration of optional features and example configuration please refer to the item(s) delivered table.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE