


EuropacPRO Perforated Rail for Connector



Perforated flat rail for connector mounting i.a.w. EN 60603-2 and DIN 41612, on VT horizontal rails.

CERTIFICERINGER



FUNKTIONER

In conjunction with rear horizontal rails, VT

For Connector Mounting in accordance with EN 60603-2, DIN 41612

SPECIFIKATIONER

Materiale:	Aluminium
Finish:	Passivated
Product Type:	Perforated Rail

Table 1/2

Katalognummer	Rack Width	Pakke mængde	Length	Produktfamilie	Works With	Certificeringer
---------------	------------	--------------	--------	----------------	------------	-----------------

20822-052	4HP	4	20.32mm	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	
20822-046	40HP	4	203.2mm	EuropacPRO	Subracks	RoHS
20822-047	60HP	4	304.8mm	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	RoHS
20822-048	84HP	4	431.8mm	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	RoHS
20822-049	28HP	4	142.24mm	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	RoHS
20822-050	42HP	4	213.36mm	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	RoHS
20822-051	20HP	4	101.6mm	EuropacPRO	Subracks	RoHS
20822-053	8HP	4	40.64mm	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO	Subracks, Cases	

Table 2/2

Katalognummer	Hurtigforsendelse
20822-052	Nej
20822-046	Nej

Katalognummer	Hurtigforsendelse
20822-047	Nej
20822-048	Nej
20822-049	Nej
20822-050	Nej
20822-051	Nej
20822-053	Nej

YDERLIGERE PRODUKTOPLYSNINGER

A threaded insert is required to secure the perforated rail on the horizontal rail.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE