


Novastar Base Plate, Multi Pieces, Open at Rear



Base plate is a plain steel blanking plate fitted to the cabinet base. Restricts air-flow into the cabinet from floor cavity and can be opened for cable ducting.

CERTIFICERINGER



FUNKTIONER

Base is open at rear for cable ducting; opening can be closed with a plain or perforated cover, filter plate or brush strip

Rear opening, width 440 mm, depth 70 mm

SPECIFIKATIONER

Product Type: Cabinet/Rack Base

Materiale: Stål

Table 1/2

Katalognummer	Bredde	Dybde	Pakke mængde	Farve	Farvekode	Finish
---------------	--------	-------	--------------	-------	-----------	--------

27230-188	553mm	500mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
27230-192	553mm	1000mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
27230-191	553mm	900mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
27230-190	553mm	800mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
27230-189	553mm	600mm	1	Black Grey	RAL 7021	Struktur Pulvermaling

Table 2/2

Katalognummer	Type	Hurtigforsendelse
27230-188	Base Plate	Nej
27230-192	Base Plate	Nej
27230-191	Base Plate	Nej
27230-190	Base Plate	Nej
27230-189	Base Plate	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Please order cover plate or brush strip separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE