

PCB Bracket



The PCB support brackets enable the fixing of a PCB to front panel. Available in different materials.



FUNKTIONER

For fixing PCB to front panel

SPECIFIKATIONER

Product Type: Bracket
Works With: Front Panels
Type: PCB Bracket

Table 1/2

Katalognummer	Materiale	Pakke mængde	Flammability Rating	Dybde	Højde	Bredde
60807-181	Zinc Alloy	1		8.6mm	11.1mm	10.2mm
60807-203	Zinc Alloy	1				
60807-183	Polybutylene Terephthalate	1	UL® 94V-0			
60807-011	Polybutylene Terephthalate	1	UL® 94V-0			
60807-211	Polybutylene Terephthalate	1	UL® 94V-0			

Table 2/2

Katalognummer	Thread Size	Thread Type	Hurtigforsendelse
60807-181	M2.5	Metric	Nej
60807-203			Nej
60807-183			Nej
60807-011			Nej

Katalognummer	Thread Size	Thread Type	Hurtigforsendelse
60807-211			Nej

YDERLIGERE PRODUKTOPLYSNINGER

Delivery is in standard pack multiples. Pricing is per individual item.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE