

Varistar CP Cross Member for seismic frame



Side crossbar to support 19" uprights in a 800 mm wide cabinet supporting 800 kg static load. The hole pattern allows easy reccessment of the 19" plane in 25 mm increments.

FUNKTIONER

Side crossbar to support 19" uprights in a 800 mm wide reinforced cabinet supporting 800 kg static load

Hole pattern allows easy reccessment of the 19" plane in 25 mm increments

SPECIFIKATIONER

Table 1/2

Katalognummer	Works With	Materiale	Finish	Farve	Farvekode	Dybde
24630-217	Varistar CP	Stål	Struktur Pulvermaling	Black Grey	RAL 7021	900mm
24630-216	Varistar CP	Stål	Struktur Pulvermaling	Black Grey	RAL 7021	800mm
24630-215	Varistar CP	Stål	Struktur Pulvermaling	Black Grey	RAL 7021	600mm

Table 2/2

Katalognummer	Pakke mængde	Pakkeenhed	Hurtigforsendelse
24630-217	4	Pair	Nej
24630-216	4	Pair	Nej
24630-215	4	Pair	Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE