

Varistar Depth Member



Horizontal depth member in the cabinet depth. Mounted directly at the Varistar CP frame for cable management, increased frame stiffness and additional fixing points.

CERTIFICERINGER



FUNKTIONER

Cable routing facilitated using cable ties and cable eyes, required for recessed shelf

St, 1.5 mm, finish AlZn

SPECIFIKATIONER

Højde:	135mm
Product Type:	Bracket
Materiale:	Stål
Works With:	Varistar CP

Table 1/1

Katalognummer	Dybde	Pakke mængde	Finish	Rack Height	Pakkeenhed	Hurtigforsendelse
23130-081	600mm	2	Aluminum-Zinc Plated	3U	Pair	Nej
23130-365	1200mm	2	Aluminum-Zinc Plated	3U	Pair	Nej
23130-083	900mm	2	Aluminum-Zinc Plated	3U	Pair	Nej
23130-364	1100mm	2	Aluminum-Zinc Plated	3U	Pair	Nej
23130-082	800mm	2	Aluminum-Zinc Plated	3U	Pair	Nej
23130-084	1000mm	2	Aluminum-Zinc Plated	3U	Pair	Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE