

VMEbus ADC / MDC J1 Backplane



The nVent SCHROFF VMEbus Backplanes have outstanding high-frequency noise suppression and very high MTBF values due to ceramic capacitors and SMD fabrication technology.

FUNKTIONER

In accordance with ANSI/VITA 1-1994 VME64 standard

3 U with J1 plane

Connection or isolation between the digital GND and chassis GND can be changed via screw

Termination active/passive, switchable via jumpers; passive termination preset

Automatic daisy chain (ADC)

Supply voltages provided via power bugs (ring tag M4) or FASTON

SPEKIFIKATIONER

Table 1/2

Katalognummer	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23001-121	Backplane	21	3U	VMEbus, J1, with ADC	Slot 1 Left	4HP
23001-120	Backplane	20	3U	VMEbus, J1, with ADC	Slot 1 Left	4HP
23001-113	Backplane	13	3U	VMEbus, J1, with ADC	Slot 1 Left	4HP
23001-112	Backplane	12	3U	VMEbus, J1, with ADC	Slot 1 Left	4HP
23001-110	Backplane	10	3U	VMEbus, J1, with ADC	Slot 1 Left	4HP

Katalognummer	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23001-109	Backplane	9	3U	VMEbus, J1, with ADC	Slot 1 Left	4HP
23001-106	Backplane	6	3U	VMEbus, J1, with ADC	Slot 1 Left	4HP
23001-105	Backplane	5	3U	VMEbus, J1, with ADC	Slot 1 Left	4HP
23001-103	Backplane	3	3U	VMEbus, J1, with ADC	Slot 1 Left	4HP
23001-104	Backplane	4	3U	VMEbus, J1, with ADC	Slot 1 Left	4HP

Table 2/2

Katalognummer	Connector Type	Power Connector Type	Utility Connector Type	Pakke mængde	Hurtigforsendelse
23001-121	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	1	Nej
23001-120	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	1	Nej
23001-113	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	1	Nej
23001-112	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	1	Nej
23001-110	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	1	Nej
23001-109	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	1	Nej
23001-106	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	1	Nej
23001-105	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	1	Nej
23001-103	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	1	Nej
23001-104	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	1	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Other configurations available on request.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE