

Clean Tray 90-Grad Winkelstück



Clean Tray 90-Degree Elbows are used for right-angle installations. The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown.

MERKMALE

Clean Tray 90-Degree Elbows are used for right-angle installations

The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown

SPEZIFIKATIONEN

Oberfläche: Gebürstet Nr. 3

Material: Edelstahl 304

Table 1/1

Katalognummer	Typ	Höhe	Breite	Dicke	Schnelles Schiff
CT22EFC90SS	Winkelstück	51mm	51mm	1.27mm	No
CT22EFCNT90SS	Winkelstück	51mm	51mm	1.27mm	No
CT22EIC90SS	Winkelstück	51mm	51mm	1.27mm	No
CT22EOC90SS	Winkelstück	51mm	51mm	1.27mm	No
CT22PEFC90SS	Winkelstück	51mm	51mm	1.27mm	No
CT33EFC90SS	Winkelstück	76mm	76mm	1.27mm	No
CT33EIC90SS	Winkelstück	76mm	76mm	1.27mm	No
CT33EOC90SS	Winkelstück	76mm	76mm	1.27mm	No
CT44EFC90SS	Winkelstück	102mm	102mm	1.27mm	No
CT44EFCNT90SS	Winkelstück	102mm	102mm	1.27mm	No
CT44EIC90SS	Winkelstück	102mm	102mm	1.27mm	No
CT44EOC90SS	Winkelstück	102mm	102mm	1.27mm	No
CT44PEFC90SS	Winkelstück	102mm	102mm	1.27mm	No
CT46EFC90SS	Winkelstück	102mm	152mm	1.27mm	No
CT46EIC90SS	Winkelstück	102mm	152mm	1.27mm	No
CT46EOC90SS	Winkelstück	102mm	152mm	1.27mm	No
CT66EFC90SS	Winkelstück	152mm	152mm	1.27mm	No

Katalognummer	Typ	Höhe	Breite	Dicke	Schnelles Schiff
CT66EFCNT90SS	Winkelstück	152mm	152mm	1.27mm	No
CT66EIC90SS	Winkelstück	152mm	152mm	1.27mm	No
CT66EOC90SS	Winkelstück	152mm	152mm	1.27mm	No
CTS33EFC90SS	Winkelstück	76mm	76mm	1.27mm	No
CTS33PEFC90SS	Winkelstück	76mm	76mm	1.27mm	No
CTS44EFC90SS	Winkelstück	102mm	102mm	1.27mm	No
CTS44PEFC90SS	Winkelstück	102mm	102mm	1.27mm	No
CTS46EFC90SS	Winkelstück	102mm	152mm	1.27mm	No
CTS46PEFC90SS	Winkelstück	102mm	152mm	1.27mm	No
CTS66EFC90SS	Winkelstück	152mm	152mm	1.27mm	No
CTS66PEFC90SS	Winkelstück	152mm	152mm	1.27mm	No
CT33EFCNT90SS	Winkelstück	76mm	76mm	1.27mm	No
CT33PEFC90SS	Winkelstück	76mm	76mm	1.27mm	No
CT46EFCNT90SS	Winkelstück	102mm	152mm	1.27mm	No
CT46PEFC90SS	Winkelstück	102mm	152mm	1.27mm	No
CT66PEFC90SS	Winkelstück	152mm	152mm	1.27mm	No

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. Alle Marken und Logos von nVent sind Eigentum der nVent Services GmbH oder ihrer Tochtergesellschaften oder durch sie lizenziert. Alle übrigen Marken sind Eigentum ihrer jeweiligen Inhaber. nVent behält sich das Recht vor, ohne Vorankündigung Änderungen vorzunehmen.

Dieses Dokument ist systemgeneriert.