


MultipacPRO Front Handle, One-Piece, Width 10 mm



The front handles can be mounted and provide an easier to mount assembly. The handles can be assembled from the front side.

CERTIFICERINGER



FUNKTIONER

Load-carrying capacity 30 kg/pair

Assembly on the front panel

Can be used for the aluminium or sheet metal versions

SPECIFIKATIONER

Materiale:	Aluminium
Finish:	Anodized
Works With:	Chassis; Front Panels
Produktfamilie:	MultipacPRO; Frame Type Plug-In Unit
Product Type:	Handle

Table 1/1

Katalognummer	Rack Height	Pakke mængde	Håndtagstype	Farve	Bredde	Hurtigforsendelse
20860-256	1U	2	Straight	Silver	10mm	Nej
20860-257	2U	2	Straight	Silver	10mm	Nej

Katalognummer	Rack Height	Pakke mængde	Håndtagstype	Farve	Bredde	Hurtigforsendelse
20860-258	3U	2	Straight	Silver	10mm	Nej
20860-259	4U	2	Straight	Silver	10mm	Nej
20860-260	5U	2	Straight	Silver	10mm	Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE