


RatiopacPRO AIR Radial Fan Unit



Simple mountable radial Fan Unit for RatiopacPRO AIR, with a air capacity of 36 m³/h (free blowing) per fan. Available in 4 widths and 2 depths and with up to 3 fans equipped.

CERTIFICERINGER



FUNKTIONER

Ball-bearing radial fans

Air capacity 36 m³/h (free blowing) per fan

Fits for RatiopacPRO Air cases (fan unit needs only 0,5 U height)

Only 1/2 U height

Air exhaust via perforation in cover plate

No restriction to rear mounting space

No mechanical modification of the case necessary

Simple mounting

SPECIFIKATIONER

Materiale:	Aluminium
Works With:	Cases
Product Type:	Fan
Type:	Radial Fan
Produktfamilie:	RatiopacPRO AIR

Table 1/1

Katalognummer	Rack Width	Spænding DC	Luftstrøm	Dybde	Bredde	Hurtigforsendelse
---------------	------------	-------------	-----------	-------	--------	-------------------

24572-408	28HP	12V	36m³/h	220mm	146.87mm	Nej
24572-405	42HP	12V	36m³/h	160mm	218mm	Nej
24572-409	42HP	12V	36m³/h	220mm	218mm	Nej
24572-406	63HP	12V	36m³/h	160mm	324.67mm	Nej
24572-410	63HP	12V	36m³/h	220mm	324.67mm	Nej
24572-407	84HP	12V	36m³/h	160mm	431.35mm	Nej
24572-411	84HP	12V	36m³/h	220mm	431.35mm	Nej
24572-404	28HP	12V	36m³/h	160mm	146.87mm	Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE