


Telescopic Slide Universal, 2 U

Universal Telescopic Slide with > 100 % extension and up to 61 kg load capacity.



CERTIFICERINGER



FUNKTIONER

Rail width k = 16 mm, max. installation width of extension/drawer w = 417 mm

Lateral mounting on the 19" uprights (19" plane remains free for fixing of the extension/drawer)

Locking at full extension

Extension length > 100 %

Static load-carrying capacity per pair 46 - 61 kg

SPECIFIKATIONER

Materiale:	Stål
Product Type:	Telescopic Slide
Finish:	Forzinket Stål

Table 1/1

Katalognummer	Length	Pakke mængde	Static Load	Type	Hurtigforsendelse
20110-100	305mm	2	61kg	Universal	Nej

Katalognummer	Length	Pakke mængde	Static Load	Type	Hurtigforsendelse
20110-101	356mm	2	60kg	Universal	Nej
20110-102	406mm	2	58kg	Universal	Nej
20110-105	559mm	2	52kg	Universal	Nej
20110-103	457mm	2	57kg	Universal	Nej
20110-104	508mm	2	55kg	Universal	Nej
20110-106	610mm	2	50kg	Universal	Nej
20110-107	660mm	2	48kg	Universal	Nej
20110-108	711mm	2	46kg	Universal	Nej

YDERLIGERE PRODUKTOPLYSNINGER

To mount on 19" plane please order assembly kit separately. Universal telescopic Rails can also be fitted without additional components in non-standard applications, thus also in other than 19" cabinets.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE