

EuropacPRO 19" Subrack Kit for Backplane, Rugged, Shielded

Power Utilities

Subrack with reinforced horizontal rails and side panels for backplane mounting.



ZERTIFIZIERUNGEN



MERKMALE

Subrack with side panel and horizontal rail, type R "rugged" with 3 hole fixing for increased stability (+60% compared to 2 hole fixing of "Heavy" rails)

Aluminum construction

Rear horizontal rail for backplane mounting with insulation strip. Special adaptor rails allow conduction cooled assemblies to be fitted

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, - 102, -103, IEEE 1101.1, IEEE 1101.10

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

IP 20, in accordance with IEC 60529

Shock and vibration tested to MIL 167, IEC 61587 DL 3, MIL 810 G, MIL 901D. Shock and vibration resistant in all three axial directions.

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available. Subrack with telescoping slides can be adopted for cabinet mounting on request

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Höhe Gestell	Tiefe	Anzahl Verpackungen	Zur Montage	Leiterplattentiefe	Typ Dichtung
24567-449	6 U	295 mm	1	Rückwandplatte	160 mm	Textile
24567-149	3 U	295 mm	1	Rückwandplatte	160 mm	Textile

Table 2/3

Katalognummer	Schock- und Vibrationstoleranz	Griff enthalten	Befestigung	Entspricht	EMV-Schirmung	Produkttyp
24567-449	25 g (force)	Ja	Gestell	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11, MIL 167, MIL 810 G, MIL 901 D, IEC 61587 DL3	Ja	Baugruppenträger/Einschub
24567-149	25 g (force)	Ja	Gestell	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11, MIL 167, MIL 810 G, MIL 901 D, IEC 61587 DL3	Ja	Baugruppenträger/Einschub

Table 3/3

Katalognummer	Breite Gestell	Statische Last
24567-449	84 HP	25 kgf
24567-149	84 HP	25 kgf

ZUSÄTZLICHE PRODUKTDDETAILS

Test reports online.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE