

Varistar CP Deco Cabinet With 19" Panel Mounts in Deco Frame

Energieversorger

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

EIGENSCHAFTEN

Open at front (no door)

19" panel mounts integrated into decoration frame

Rear door with single point locking, side panels with quick release fastener

Static load-carrying capacity 400 kg (mounted at decoration frame)

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Höhe	Frame Color	Breite	Frame Color Code	Cladding Material
10630-033	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Stahl
10630-034	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Stahl
10630-035	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Stahl
10630-036	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Stahl

Table 2/3

Katalognummer	Tiefe	Cladding Color	Cladding Color Code	Konform mit	Frame Material	Product Type
---------------	-------	----------------	---------------------	-------------	----------------	--------------

10630-033	600 mm	Black Grey	RAL 7021	IEC 60297-3-100	Stahl	Schrank
10630-034	800 mm	Black Grey	RAL 7021	IEC 60297-3-100	Stahl	Schrank
10630-035	600 mm	Black Grey	RAL 7021	IEC 60297-3-100	Stahl	Schrank
10630-036	800 mm	Black Grey	RAL 7021	IEC 60297-3-100	Stahl	Schrank

Table 3/3

Katalognummer	Statische Last
10630-033	400 kgf
10630-034	400 kgf
10630-035	400 kgf
10630-036	400 kgf

ADDITIONAL PRODUCT DETAILS

Lever handle can be added to rear door.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE