


ACS-30 Erfassungs- und Überwachungs-Modul



The nVent RAYCHEM ACS-30-EU-ELEXANT650C-SMDI-MOD Module for the ACS-30 system provides smart sensor input for surface snow melting and roof & gutter de-icing applications. The Remote Monitoring Module (RMM) is used to collect sensor/temperature inputs for monitoring of the heat tracing circuits of an ACS-30 control system.

EIGENSCHAFTEN

- The output from the ACS-30-EU-ELEXANT650C-SMDI-MOD module enables the switching of the heating circuits within the power & control module (PCM)
- The ACS-30-EU-ELEXANT650C-SMDI-MOD module provides ground or roof & gutter temperature and moisture sensing for the ACS-30 control system
- Ground temperature and moisture sensor (E650C-G) and roof & gutter temperature and moisture sensor (E650C-R) are sold separately
- The RMM provides up to 8 sensor inputs per module with feedback to the ACS-30-EU-UIT3 interface
- A single twisted pair RS-485 cable connects up to 247 RMM units providing additional temperature monitoring sensor inputs
- The RMM is remotely located adjacent to the desired measurement locations
- The RMM comes in 2 versions: ACS-30-EU-RMM3 (230 V) and ACS-30-EU-RMM3-24VDC (24 V), both pre-installed inside a compact enclosure

SPEZIFIKATIONEN

Table 1/2						
Katalognummer	Artikelname	Tiefe	Höhe	Gehäusewerkstoff	Schutzart	Montage
2000003973	ACS-30-EU-ELEXANT650C-SMDI-MOD	132 mm	262 mm	Polykarbonat	IP20	Wandmontage

Table 2/2		
Katalognummer	Artikelname	Breite

2000003973	ACS-30-EU-ELEXANT650C-SMDI-MOD	332 mm
------------	--------------------------------	--------

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

Nordamerika

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asien-Pazifik

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Lateinamerika

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT