

Assembly Parts for Rugged Components

Energieversorger



Assembly parts with thread-locking compound for rugged Side Panel, horizontal rail, cover plates, rear angle.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Screws for the following fixings: Rugged side panel - horizontal rail, Rugged side panel - cover plate, Rugged side panel - rear angle

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Typ	Länge	Package Quantity	Gewindegröße	Material	Product Family
24566-105	Countersunk Screw	7 mm	100	M4	Edelstahl	EuropacPRO
24566-104	Panhead Screw	8 mm	100	M4	Edelstahl	EuropacPRO
24566-103	Panhead Screw	10 mm	100	M4	Edelstahl	EuropacPRO
24566-106	Countersunk Screw	10 mm	100	M4	Edelstahl	EuropacPRO

Katalognummer	Typ	Länge	Package Quantity	Gewindegröße	Material	Product Family
24566-101	Countersunk Screw	14 mm	100	M4	Edelstahl	EuropacPRO
24566-102	Panhead Screw	14 mm	100	M4	Edelstahl	EuropacPRO
24566-100	Countersunk Screw	18 mm	100	M4	Edelstahl	EuropacPRO
24560-140	Square Nut		100		Edelstahl	EuropacPRO

Table 2/2

Katalognummer	Product Type	Kompatibel mit
24566-105	Assembly Kit	Baugruppenträger
24566-104	Assembly Kit	Baugruppenträger
24566-103	Assembly Kit	Baugruppenträger
24566-106	Assembly Kit	Baugruppenträger
24566-101	Assembly Kit	Baugruppenträger
24566-102	Assembly Kit	Baugruppenträger
24566-100	Assembly Kit	Baugruppenträger
24560-140	Assembly Kit	Baugruppenträger

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE