

EuropacPRO 19" Subrack Kit for DIN Connector, Slide Rail, Retrofit Shielding

Energieversorger



Non-shielded subrack for Din Connector mounting EN 60603-2 , Subrack can be assembled on slide rails to support the subrack inside a cabinet.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Subrack with side panel type F ("flexible"), 19" bracket with notch for slide rail assembly

Installed load up to 11 kg

Subrack can be used with slide rails

Horizontal rails, rear, for connector mounting (IEC 60603-2 / DIN 41612)

Threaded insert pre-fitted

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Tiefe	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24553-192	3 U	235 mm	1	DIN Connector	160 mm, 220 mm	Edelstahl

Katalognummer	Rack Height	Tiefe	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24553-193	3 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Edelstahl
24553-194	3 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Edelstahl
24553-492	6 U	235 mm	1	DIN Connector	160 mm, 220 mm	Edelstahl
24553-493	6 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Edelstahl
24553-494	6 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Edelstahl

Table 2/3

Katalognummer	Handle Included	Montage	Konform mit	EMC Shielding	Product Type	Rack Width
24553-192	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24553-193	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24553-194	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24553-492	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24553-493	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24553-494	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP

Table 3/3

Katalognummer	Statische Last
24553-192	11 kgf
24553-193	11 kgf
24553-194	11 kgf
24553-492	11 kgf

Katalognummer	Statische Last
24553-493	11 kgf
24553-494	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE