


# EuropacPRO 19" Subrack Kit for Railway, Shielded, SNCF

## Energieversorger

Subrack for Railway applications, conform to SNCF Standard.



### ZERTIFIZIERUNGEN



### EIGENSCHAFTEN

SNCF listed, EuropacPRO-fer, tested to NF F 61-005 and NF F 60-002

The 19" bracket is firmly fixed to the side panel (tox-cold welded) and is especially suited for high mechanical stresses (vibration resistance)

Lateral support bars to NFF standard facilitate insertion of subrack into the (cabinet) frame. The double 19" screwing position adds to additionally safety (NFF standard)

IP 20, in accordance with IEC 60529

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Aluminum construction

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

## SPEZIFIKATIONEN

Table 1/3

| Katalognummer | Rack Height | Rack Width | Package Quantity | For Mounting | Board Depth | EMC Gasket Type |
|---------------|-------------|------------|------------------|--------------|-------------|-----------------|
| 21500-028     | 6 U         | 84 HP      | 1                | Backplane    | 220 mm      | Textile         |
| 21500-030     | 3 U         | 84 HP      | 1                | Backplane    | 220 mm      | Textile         |
| 21500-068     | 3 U         | 36 HP      | 1                | Backplane    | 220 mm      | Textile         |
| 21500-071     | 6 U         | 36 HP      | 1                | Backplane    | 220 mm      | Textile         |

Table 2/3

| Katalognummer | Shock and Vibration Tolerance | Handle Included | Montage | Konform mit                                     | Tiefe  | EMC Shielding |
|---------------|-------------------------------|-----------------|---------|-------------------------------------------------|--------|---------------|
| 21500-028     | 5 g (force)                   | Ja              | Rack    | IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002 | 320 mm | Ja            |
| 21500-030     | 5 g (force)                   | Ja              | Rack    | IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002 | 320 mm | Ja            |
| 21500-068     | 5 g (force)                   | Ja              | Rack    | IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002 | 320 mm | Ja            |
| 21500-071     | 5 g (force)                   | Ja              | Rack    | IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002 | 320 mm | Ja            |

Table 3/3

| Katalognummer | Product Type    | Statische Last | Zertifizierungen |
|---------------|-----------------|----------------|------------------|
| 21500-028     | Subrack/Chassis | 15 kgf         | RoHS, SNCF       |
| 21500-030     | Subrack/Chassis | 15 kgf         | RoHS, SNCF       |
| 21500-068     | Subrack/Chassis | 15 kgf         | RoHS             |

| Katalognummer | Product Type    | Statische Last | Zertifizierungen |
|---------------|-----------------|----------------|------------------|
| 21500-071     | Subrack/Chassis | 15 kgf         | RoHS             |

## ADDITIONAL PRODUCT DETAILS

Fer = ferroviaire = French Railways, 1 T = 4 HP = 20.32 mm.

Receptacle/mounting frame for subracks, stainless steel, 9 T or 21 T on request.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**