We connect and protect

Varistar CP Cabinet Frame, Seismic

Energieversorger

Welded, steel enclosure engineered specifically to protect equipment in areas with seismic activity and satisfy Bellcore Zore 4 requirements.

EIGENSCHAFTEN

St, 1.5 mm, zinc-plated, finish: powder-coated

Earthquake resistance to Bellcore Zone 4

Welded seismic frame with strengthening brackets, RAL 7021

Dynamic load-carrying capacity 250 kg to IEC 61587-2

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Höhe	Breite	Tiefe	Shock and Vibration Tolerance	Farbe
20630-358	33 U	1600 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-359	33 U	1600 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-360	33 U	1600 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-361	33 U	1600 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-362	38 U	1800 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-363	38 U	1800 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-364	38 U	1800 mm	800 mm	600 mm	5 g (force)	Black Grey

Katalognummer	Rack Height	Höhe	Breite	Tiefe	Shock and Vibration Tolerance	Farbe
20630-365	38 U	1800 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-366	42 U	2000 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-367	42 U	2000 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-368	42 U	2000 mm	600 mm	1000 mm	5 g (force)	Black Grey
20630-369	42 U	2000 mm	600 mm	1200 mm	5 g (force)	Black Grey
20630-370	42 U	2000 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-371	42 U	2000 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-372	42 U	2000 mm	800 mm	1000 mm	5 g (force)	Black Grey
20630-373	42 U	2000 mm	800 mm	1200 mm	5 g (force)	Black Grey
20630-374	47 U	2200 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-375	47 U	2200 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-376	47 U	2200 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-377	47 U	2200 mm	800 mm	800 mm	5 g (force)	Black Grey

Table 2/3

Katalognummer	Color Code	Konform mit	Frame Material	Material	Product Type	Statische Last
20630-358	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-359	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-360	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf

Katalognummer	Color Code	Konform mit	Frame Material	Material	Product Type	Statische Last
20630-361	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-362	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-363	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl		Cabinet/Rack Frame	1600 kgf
20630-364	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-365	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-366	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-367	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-368	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-369	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-370	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-371	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-372	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-373	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-374	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-375	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-376	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf
20630-377	RAL 7021	IEC 61587-1, IEC 61587-2	Stahl	Stahl	Cabinet/Rack Frame	1600 kgf

Table 3/3

Katalognummer	Typ	Kompatibel mit

20630-358	Seismisch	Varistar CP
20630-359	Seismisch	Varistar CP
20630-360	Seismisch	Varistar CP
20630-361	Seismisch	Varistar CP
20630-362	Seismisch	Varistar CP
20630-363	Seismisch	Varistar CP
20630-364	Seismisch	Varistar CP
20630-365	Seismisch	Varistar CP
20630-366	Seismisch	Varistar CP
20630-367	Seismisch	Varistar CP
20630-368	Seismisch	Varistar CP
20630-369	Seismisch	Varistar CP
20630-370	Seismisch	Varistar CP
20630-371	Seismisch	Varistar CP
20630-372	Seismisch	Varistar CP
20630-373	Seismisch	Varistar CP
20630-374	Seismisch	Varistar CP
20630-375	Seismisch	Varistar CP
20630-376	Seismisch	Varistar CP

20630-377	Seismisch	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order attachments and components separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.