

EuropacPRO 19" Subrack Kit for Backplane, Slide Rail, Retrofit Shielding

Energieversorger



Non-shielded subrack for backplane, subrack can be assembled on slide rails to support the subrack inside a cabinet.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Subrack with side panel type F ("Flexible"), 19" bracket is depth-adjustable

Subrack can be used with slide rails

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 11 kg

Threaded insert, insulation strip pre-fitted

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Tiefe	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24553-132	3 U	235 mm	1	Backplane	160 mm, 220 mm	Edelstahl

Katalognummer	Rack Height	Tiefe	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24553-133	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Edelstahl
24553-134	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Edelstahl
24553-432	6 U	235 mm	1	Backplane	160 mm, 220 mm	Edelstahl
24553-433	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Edelstahl
24553-434	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Edelstahl

Table 2/3

Katalognummer	Handle Included	Montage	Konform mit	EMC Shielding	Product Type	Rack Width
24553-132	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24553-133	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24553-134	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24553-432	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24553-433	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24553-434	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP

Table 3/3

Katalognummer	Statische Last
24553-132	11 kgf
24553-133	11 kgf
24553-134	11 kgf
24553-432	11 kgf

Katalognummer	Statische Last
24553-433	11 kgf
24553-434	11 kgf

ADDITIONAL PRODUCT DETAILS

Alternative product for older EuropacLab and Europac subrack series.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE