

Varistar CP Plain Steel Door, Seismic IP55, With Multi-Point Locking

Energieversorger

IP55 Seismic Steel Door with lever handle and multi-Point locking.

EIGENSCHAFTEN

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for EMC applications

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Höhe	Breite	Farbe	Color Code	Konform mit
21630-752	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-753	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-754	38 U	600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-2, IEC 61587-2, IEC 60529
21630-755	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-756	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-757	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529

Katalognummer	Rack Height	Höhe	Breite	Farbe	Color Code	Konform mit
21630-758	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-759	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529

Table 2/3

Katalognummer	Locking Type	Material	Product Type	Protection Rating	Rack Width	Typ
21630-752	4-Point Locking	Stahl	Cabinet Door	IP55		Steel Door, Plain
21630-753	4-Point Locking	Stahl	Cabinet Door	IP55	800 HP	Steel Door, Plain
21630-754	4-Point Locking	Stahl	Cabinet Door	IP55		Steel Door, Plain
21630-755	4-Point Locking	Stahl	Cabinet Door	IP55		Steel Door, Plain
21630-756	4-Point Locking	Stahl	Cabinet Door	IP55		Steel Door, Plain
21630-757	4-Point Locking	Stahl	Cabinet Door	IP55		Steel Door, Plain
21630-758	5-Point Locking	Stahl	Cabinet Door	IP55		Steel Door, Plain
21630-759	5-Point Locking	Stahl	Cabinet Door	IP55		Steel Door, Plain

Table 3/3

Katalognummer	Kompatibel mit
21630-752	Varistar CP
21630-753	Varistar CP
21630-754	Varistar CP
21630-755	Varistar CP
21630-756	Varistar CP

Katalognummer	Kompatibel mit
21630-757	Varistar CP
21630-758	Varistar CP
21630-759	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE