

Varistar CP Swing Frame for 800 mm Width

Energieversorger

The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° / 160° movement and flexible pivot point.

EIGENSCHAFTEN

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" subracks

120° / 160° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Rack Height	Farbe	Color Code	Höhe	Material	Product Type
21630-669	24 U	Black Grey	RAL 7021	1200 mm	Stahl	Cabinet/Rack Frame
21630-680	24 U	Black Grey	RAL 7021	1200 mm	Stahl	Cabinet/Rack Frame
21630-671	29 U	Black Grey	RAL 7021	1400 mm	Stahl	Cabinet/Rack Frame
21630-681	29 U	Black Grey	RAL 7021	1400 mm	Stahl	Cabinet/Rack Frame
21630-673	33 U	Black Grey	RAL 7021	1600 mm	Stahl	Cabinet/Rack Frame
21630-682	33 U	Black Grey	RAL 7021	1600 mm	Stahl	Cabinet/Rack Frame
21630-675	38 U	Black Grey	RAL 7021	1800 mm	Stahl	Cabinet/Rack Frame

Katalognummer	Rack Height	Farbe	Color Code	Höhe	Material	Product Type
21630-683	38 U	Black Grey	RAL 7021	1800 mm	Stahl	Cabinet/Rack Frame
21630-677	42 U	Black Grey	RAL 7021	2000 mm	Stahl	Cabinet/Rack Frame
21630-684	42 U	Black Grey	RAL 7021	2000 mm	Stahl	Cabinet/Rack Frame
21630-679	47 U	Black Grey	RAL 7021	2200 mm	Stahl	Cabinet/Rack Frame
21630-685	47 U	Black Grey	RAL 7021	2200 mm	Stahl	Cabinet/Rack Frame

Table 2/2

Katalognummer	Protection Rating	Breite
21630-669	IP20	800 mm
21630-680	IP20	800 mm
21630-671	IP20	800 mm
21630-681	IP20	800 mm
21630-673	IP20	800 mm
21630-682	IP20	800 mm
21630-675	IP20	800 mm
21630-683	IP20	800 mm
21630-677	IP20	800 mm
21630-684	IP20	800 mm
21630-679	IP20	800 mm
21630-685	IP20	800 mm

ADDITIONAL PRODUCT DETAILS

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE