

Internal side panels | Stromverteilung, MSPS



The galvanised steel internal side panels, MSPS, segregate vertical sections and allow for mounting of busbar supports, MSHS, as well as other accessories. It is a flexible solution both for fix and plug in systems and allows for meeting form 4 segregation according to IEC 61439.

MERKMALE

Beschreibung: Internal side panels to build up sections as from the enclosure frame. Frame hole pattern is needed in front, rear, top and bottom.

Material: 1.5 mm galvanized steel.

Lieferumfang: 1 piece with mounting material.

The side panels segregate vertical sections, allowing customer's to mount main busbar supports (MSHS) and other accessories

A flexible solution for both fix and plug-in systems

The side panels allow customers to build up power distribution configurations to meet form 4 segregation according to IEC 61439

Hole patterns are required in the top, bottom, front and rear of the enclosure, in order to mount the internal side panels

SPEZIFIKATIONEN

Dicke: 1.5mm
Oberfläche: Verzinkt
Material: Stahl

Table 1/1

Katalognummer	Höhe	Breite	Tiefe	Plattengröße	Gehäusematerial	Produktfamilie
MSPS1803	1800mm	88.5mm	300mm	1800 x 337mm	Baustahl	Freistehend
MSPS1805	1800mm	88.5mm	500mm	1800 x 337mm	Baustahl	Freistehend
MSPS1806	1800mm	26mm	600mm	1800 x 507mm	Baustahl	Freistehend
MSPS1806F	1800mm	26mm	600mm	1800 x 507mm	Baustahl	Freistehend
MSPS1808	1800mm	26mm	800mm	1800 x 507mm	Baustahl	Freistehend
MSPS1808F	1800mm	26mm	800mm	1800 x 507mm	Baustahl	Freistehend
MSPS2003	2000mm	88.5mm	300mm	2000 x 337mm	Baustahl	Freistehend
MSPS2005	2000mm	88.5mm	500mm	2000 x 337mm	Baustahl	Freistehend
MSPS2006	2000mm	26mm	600mm	2000 x 507mm	Baustahl	Freistehend
MSPS2006F	2000mm	26mm	600mm	2000 x 507mm	Baustahl	Freistehend
MSPS2008	2200mm	26mm	800mm	2200 x 507mm	Baustahl	Freistehend
MSPS2008F	2000mm	26mm	800mm	2000 x 507mm	Baustahl	Freistehend
MSPS2203	2200mm	88.5mm	300mm	2200 x 337mm	Baustahl	Freistehend
MSPS2205	2200mm	88.5mm	500mm	2200 x 337mm	Baustahl	Freistehend
MSPS2206	2200mm	26mm	600mm	2200 x 507mm	Baustahl	Freistehend
MSPS2206F	2200mm	26mm	600mm	2200 x 507mm	Baustahl	Freistehend
MSPS2208	2200mm	26mm	800mm	2200 x 507mm	Baustahl	Freistehend

Katalognummer	Höhe	Breite	Tiefe	Plattengröße	Gehäusematerial	Produktfamilie
MSPS2208F	2200mm	26mm	800mm	2200 x 507mm	Baustahl	Freistehend

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE