

EuropacPRO 19" Subrack Kit for Backplane, Light, Unshielded

Energieversorger

Non-EMC shielded subrack for backplane mounting, light version.



ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Subrack with side panel type L ("light") with integrated 19" support brackets

Horizontal rail type "light"

Aluminum construction

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 7.5 kg

Supplied as space-saving flat-pack

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Modifications such as cutouts, different finishes or dimensions available

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Rack Height	Tiefe	Package Quantity	For Mounting	Board Depth	Handle Included
24564-131	3 U	175 mm	1	Backplane	160 mm	Nein
24564-132	3 U	235 mm	1	Backplane	160 mm, 220 mm	Nein
24564-133	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Nein
24564-431	6 U	175 mm	1	Backplane	160 mm	Nein
24564-432	6 U	235 mm	1	Backplane	160 mm, 220 mm	Nein
24564-433	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Nein

Table 2/2

Katalognummer	Montage	Konform mit	EMC Shielding	Product Type	Rack Width	Statische Last
24564-131	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Nein	Subrack/Chassis	84 HP	7.5 kgf
24564-132	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Nein	Subrack/Chassis	84 HP	7.5 kgf
24564-133	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Nein	Subrack/Chassis	84 HP	7.5 kgf
24564-431	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Nein	Subrack/Chassis	84 HP	7.5 kgf
24564-432	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Nein	Subrack/Chassis	84 HP	7.5 kgf
24564-433	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Nein	Subrack/Chassis	84 HP	7.5 kgf

ADDITIONAL PRODUCT DETAILS

Subrack is not prepared for shielding, retrofit for protection class IP 20 possible

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE