


Horizontal Perforated Strip

Energieversorger



Perforated strip out of 1mm Aluminum for centering shielded plug-in units.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

For centering the shielded plug-in units

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Rack Width	Package Quantity	Länge	Material	Product Family	Product Type
30845-253	84 HP	1	431.6 mm	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Perforated Strip

Katalognummer	Rack Width	Package Quantity	Länge	Material	Product Family	Product Type
30845-197	28 HP	1	147.12 mm	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Perforated Strip
30845-211	42 HP	1	218.24 mm	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Perforated Strip
30845-232	63 HP	1	324.92 mm	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Perforated Strip

Table 2/2

Katalognummer	Kompatibel mit
30845-253	Subracks, Cases
30845-197	Subracks, Cases
30845-211	Subracks, Cases
30845-232	Subracks, Cases

ADDITIONAL PRODUCT DETAILS

Only usable with double-T threaded insert.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-

Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE