

Novastar Perforated Steel Door

Energieversorger



Perforated doors allow 60 % ventilation thus allowing better passive cooling. Novastar perforated doors come with 180° opening angle and aesthetic looks.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Can be mounted at front and rear

Perforated (60 % ventilation opening)

Opening angle 180°

Lock with key (2233X)

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Rack Height	Höhe	Breite	Farbe	Color Code	Product Type
25230-081	6 U	288.4 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-081	6 U	288.4 mm	553 mm	Light Grey	RAL 7035	Cabinet Door

Katalognummer	Rack Height	Höhe	Breite	Farbe	Color Code	Product Type
25230-082	9 U	421.75 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-082	9 U	421.75 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-083	12 U	555.1 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-083	12 U	555.1 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-084	16 U	732.9 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-084	16 U	732.9 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-085	20 U	910.7 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-085	20 U	910.7 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-086	25 U	1132.95 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-086	25 U	1132.95 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-091	29 U	1310.75 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-091	29 U	1310.75 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-087	34 U	1533 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-087	34 U	1533 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-088	38 U	1710.8 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-088	38 U	1710.8 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-089	43 U	1933.05 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-089	43 U	1933.05 mm	553 mm	Light Grey	RAL 7035	Cabinet Door

Katalognummer	Rack Height	Höhe	Breite	Farbe	Color Code	Product Type
25230-090	47 U	2110.85 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-090	47 U	2110.85 mm	553 mm	Light Grey	RAL 7035	Cabinet Door

Table 2/2

Katalognummer	Typ
25230-081	Steel Door, Perforated
26230-081	Steel Door, Perforated
25230-082	Steel Door, Perforated
26230-082	Steel Door, Perforated
25230-083	Steel Door, Perforated
26230-083	Steel Door, Perforated
25230-084	Steel Door, Perforated
26230-084	Steel Door, Perforated
25230-085	Steel Door, Perforated
26230-085	Steel Door, Perforated
25230-086	Steel Door, Perforated
26230-086	Steel Door, Perforated
25230-091	Steel Door, Perforated
26230-091	Steel Door, Perforated
25230-087	Steel Door, Perforated

Katalognummer	Typ
26230-087	Steel Door, Perforated
25230-088	Steel Door, Perforated
26230-088	Steel Door, Perforated
25230-089	Steel Door, Perforated
26230-089	Steel Door, Perforated
25230-090	Steel Door, Perforated
26230-090	Steel Door, Perforated

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE