

# Varistar CP Double Steel Door, Plain, 3-Point Locking

## Energieversorger

Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

### EIGENSCHAFTEN

Double steel door with 3 point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

### SPEZIFIKATIONEN

Table 1/2

| Katalognummer | Rack Height | Höhe    | Breite | Farbe      | Color Code | Konform mit                 |
|---------------|-------------|---------|--------|------------|------------|-----------------------------|
| 21630-086     | 42 U        | 2000 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-087     | 47 U        | 2200 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-088     | 52 U        | 2450 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-089     | 42 U        | 2000 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-090     | 47 U        | 2200 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-091     | 52 U        | 2450 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-440     | 24 U        | 1200 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |

| Katalognummer | Rack Height | Höhe    | Breite | Farbe      | Color Code | Konform mit                 |
|---------------|-------------|---------|--------|------------|------------|-----------------------------|
| 21630-441     | 24 U        | 1200 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-442     | 29 U        | 1400 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-443     | 29 U        | 1400 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-444     | 33 U        | 1600 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-445     | 33 U        | 1600 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-446     | 38 U        | 1800 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-447     | 38 U        | 1800 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |

Table 2/2

| Katalognummer | Locking Type    | Product Type | Protection Rating | Typ               | Kompatibel mit |
|---------------|-----------------|--------------|-------------------|-------------------|----------------|
| 21630-086     | 3-Point Locking | Cabinet Door | IP20              | Steel Double Door | Varistar CP    |
| 21630-087     | 3-Point Locking | Cabinet Door | IP20              | Steel Double Door | Varistar CP    |
| 21630-088     | 3-Point Locking | Cabinet Door | IP20              | Steel Double Door | Varistar CP    |
| 21630-089     | 3-Point Locking | Cabinet Door | IP20              | Steel Double Door | Varistar CP    |
| 21630-090     | 3-Point Locking | Cabinet Door | IP20              | Steel Double Door | Varistar CP    |
| 21630-091     | 3-Point Locking | Cabinet Door | IP20              | Steel Double Door | Varistar CP    |
| 21630-440     | 3-Point Locking | Cabinet Door | IP20              | Steel Double Door | Varistar CP    |
| 21630-441     | 3-Point Locking | Cabinet Door | IP20              | Steel Double Door | Varistar CP    |
| 21630-442     | 3-Point Locking | Cabinet Door | IP20              | Steel Double Door | Varistar CP    |
| 21630-443     | 3-Point Locking | Cabinet Door | IP20              | Steel Double Door | Varistar CP    |

| Katalognummer | Locking Type    | Product Type | Protection Rating | Typ               | Kompatibel mit |
|---------------|-----------------|--------------|-------------------|-------------------|----------------|
| 21630-444     | 3-Point Locking | Cabinet Door | IP20              | Steel Double Door | Varistar CP    |
| 21630-445     | 3-Point Locking | Cabinet Door | IP20              | Steel Double Door | Varistar CP    |
| 21630-446     | 3-Point Locking | Cabinet Door | IP20              | Steel Double Door | Varistar CP    |
| 21630-447     | 3-Point Locking | Cabinet Door | IP20              | Steel Double Door | Varistar CP    |

## ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**