


Horizontal Pouring Basin, Side Fill



Side fill horizontal pouring basins are used when interferences of the structure will not allow top filling of the sleeve.

MERKMALE

Made from heat-resistant graphite

Durable, re-usable and long lasting

Designed for use with T-Series and B-Series horizontal side fill sleeves

SPEZIFIKATIONEN

Material: Graphit

Table 1/1

Katalognummer	Durchmesser (Ø)	Länge 1 (L1)	Länge 2 (L2)	Breite (W)	Höhe 1 (H1)	Höhe 2 (H2)
RBWS1547F	64 mm	140 mm	22 mm	76 mm	137mm	67mm
RBWS1547J	76 mm	140 mm	22 mm	76 mm	137mm	67mm
RBWS1547E	57 mm	140 mm	22 mm	76 mm	137mm	67mm
RBWS1547M	95 mm	140 mm	22 mm	76 mm	137mm	67mm
RBWS1547C	48 mm	140 mm	22 mm	76 mm	137mm	67mm
RBWS1547D	54 mm	140 mm	22 mm	76 mm	137mm	67mm

Katalognummer	Durchmesser (Ø)	Länge 1 (L1)	Länge 2 (L2)	Breite (W)	Höhe 1 (H1)	Höhe 2 (H2)
RBWS1547X	38 mm	140 mm	22 mm	76 mm	137mm	67mm


ZUSÄTZLICHE PRODUKTDDETAILS

RBWS1547 pouring basins require one RBW332 pouring basin frame (sold separately).

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System Instruction Manual.

Sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

DIAGRAMME



WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

Nordamerika

+1.800.753.9221
Option 1 – Kundendienst
Option 2 – Technischer
Support

Europa

Niederlande:
+31 800-0200135
Frankreich:
+33 800 901 793

Europa

Deutschland:
800 1890272
Sonstige Länder:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE