

Guide Rail With Coding, preassembled ESD Clip for CompactPCI/ VME64x, PC

Power Utilities

MERKMALE

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to an optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

ESD clip for an conductive contact between PCB and horizontal rail preassembled

Storage temperature: from -40 °C ... 130 °C

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Farbe	Anzahl Verpackungen	Leiterplattentiefe	Nutbreite	Entspricht	Material
24568-847	Rot	10	160 mm	2	EN 45545-2	Polycarbonat
24568-848	Grau	10	160 mm	2	EN 45545-2	Polycarbonat
24568-850	Rot	10	160 mm	2	EN 45545-2	Polycarbonat
24568-851	Grau	10	160 mm	2	EN 45545-2	Polycarbonat
24568-853	Rot	10	70 mm	2	EN 45545-2	Polycarbonat

Katalognummer	Farbe	Anzahl Verpackungen	Leiterplattentiefe	Nutbreite	Entspricht	Material
24568-854	Grau	10	70 mm	2	EN 45545-2	Polycarbonat
24568-855	Rot	10	70 mm	2	EN 45545-2	Polycarbonat
24568-856	Grau	10	70 mm	2	EN 45545-2	Polycarbonat

Table 2/2				
Katalognummer	Produktfamilie	Produkttyp	Typ	Passt zu
24568-847	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Führungsschiene	With Coding and preassembled ESD Clips	Baugruppenträger, Gehäuse, 19-Zoll- Einschub, Systeme
24568-848	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Führungsschiene	With Coding and preassembled ESD Clips	Baugruppenträger, Gehäuse, 19-Zoll- Einschub, Systeme
24568-850	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Führungsschiene	With Coding and preassembled ESD Clips	Baugruppenträger, Gehäuse, 19-Zoll- Einschub, Systeme
24568-851	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Führungsschiene	With Coding and preassembled ESD Clips	Baugruppenträger, Gehäuse, 19-Zoll- Einschub, Systeme
24568-853	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Führungsschiene	With Coding and preassembled ESD Clips	Baugruppenträger, Gehäuse, 19-Zoll- Einschub, Systeme
24568-854	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Führungsschiene	With Coding and preassembled ESD Clips	Baugruppenträger, Gehäuse, 19-Zoll- Einschub, Systeme

Katalognummer	Produktfamilie	Produkttyp	Typ	Passt zu
24568-855	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Führungsschiene	With Coding and preassembled ESD Clips	Baugruppenträger, Gehäuse, 19-Zoll- Einschub, Systeme
24568-856	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Führungsschiene	With Coding and preassembled ESD Clips	Baugruppenträger, Gehäuse, 19-Zoll- Einschub, Systeme

ZUSÄTZLICHE PRODUKTDDETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE