



Modulschiene hinten, Typ H-ST, Standard, 1000 mm

KATALOGNUMMER

34560-501



Combinations of horizontal rails and side panels

		+ can be combined		+ combination: not recommended	
Light + B Heavy + B		-	+	+	sublock kit "heavy" 
		+	sublock kit "heavy" 	sublock kit "heavy" and sublock kit "heavy" "medium" 	+
Light + L Heavy + L		sublock kit "light" 	sublock kit "heavy" 	-	-
		+	+	-	-
Horizontal rail Side panel		Light + L 	sublock kit 	Heavy + B 	Rugged + B 

Die Modulschiene vom Typ ST, ermöglicht die isolierte Montage einer Backplane. Die Isolierung erfolgt durch einen Isolierstreifen.

ZERTIFIZIERUNGEN



MERKMALE

Für indirekte Backplanebefestigung mit Isolierstreifen

Standard für hohe mechanische Beanspruchung (H-ST)

Einbau oben und unten

TE-Bedruckung erfolgt erst ab 28 TE

Aluminiumprofil, Oberfläche eloxiert, Kontaktfläche leitfähig, ohne TE-Bedruckung

PRODUKTMERKMALE

Breite Gestell: 195HP

Anzahl Verpackungen: 1

Oberfläche: Eloxiert

Länge: 1000mm

Material: Aluminium

Produktfamilie: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Produkttyp: Modulschiene

Typ: Schwer, ST

Passt zu: Baugruppenträger; Gehäuse

Net Weight: 0.304kg

ZUSÄTZLICHE PRODUKTDDETAILS

Die Lieferung erfolgt in Lieferlosgrößen. Die Preise gelten pro einzelnen Artikel.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Unser starkes markenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE