


Horizontal Rails Threaded Insert, M2.5

Energieversorger



The threaded insert is a metal strip with thread M2.5 and allows the fixing of front panels.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

The collar screws used for fixing partial-width front panels must be 12.3 mm long

Usable for all horizontal rails

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Rack Width	Package Quantity	Länge	Material	Product Family	Product Type
34561-384	84 HP	1	431.3 mm	Stahl	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Threaded Insert

Katalognummer	Rack Width	Package Quantity	Länge	Material	Product Family	Product Type
34561-328	28 HP	1	146.82 mm	Stahl	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Threaded Insert
34561-342	42 HP	1	217.94 mm	Stahl	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Threaded Insert
34561-363	84 HP	1	324.62 mm	Stahl	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac	Threaded Insert

Table 2/2

Katalognummer	Kompatibel mit
34561-384	Subracks, Cases
34561-328	Subracks, Cases
34561-342	Subracks, Cases
34561-363	Subracks, Cases

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie

zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE