

Varistar CP Base Plate, One-Piece, With Lateral Cable ducting

Energieversorger

Varistar CP Base Plate, One-Piece, With Lateral Cable ducting.

EIGENSCHAFTEN

Base plate is open at the side; the opening can be covered over with a brush strip

SPEZIFIKATIONEN

Table 1/2						
Katalognummer	Breite	Tiefe	Farbe	Color Code	Endbearbeitung	Material
21630-134	600 mm	1000 mm	Black Grey	RAL 7021	Pulverbeschichtet	Stahl
21630-135	600 mm	1100 mm	Black Grey	RAL 7021	Pulverbeschichtet	Stahl
21630-136	600 mm	1200 mm	Black Grey	RAL 7021	Pulverbeschichtet	Stahl
21630-137	800 mm	1000 mm	Black Grey	RAL 7021	Pulverbeschichtet	Stahl
21630-138	800 mm	1100 mm	Black Grey	RAL 7021	Pulverbeschichtet	Stahl
21630-139	800 mm	1200 mm	Black Grey	RAL 7021	Pulverbeschichtet	Stahl

Table 2/2		
Katalognummer	Product Type	Typ
21630-134	Cabinet/Rack Base	Base Plate, Cable Ducting

Katalognummer	Product Type	Typ
21630-135	Cabinet/Rack Base	Base Plate, Cable Ducting
21630-136	Cabinet/Rack Base	Base Plate, Cable Ducting
21630-137	Cabinet/Rack Base	Base Plate, Cable Ducting
21630-138	Cabinet/Rack Base	Base Plate, Cable Ducting
21630-139	Cabinet/Rack Base	Base Plate, Cable Ducting

ADDITIONAL PRODUCT DETAILS

Please order brush strip separately.

Please purchase the grounding kit separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE