

Varistar CP EMC Cabinet, IP 55

Energieversorger



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

EIGENSCHAFTEN

Shielding 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3)

Shielding 30 dB at 18 GHz, (tested to EN 61000-5-7) with EN45545 gaskets

Type of protection IP 55

Static load-carrying capacity 1600 kg

Doors with 4-point locking and screw-fixed side panels

Side and rear panels can be installed by one person

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Höhe	Frame Color	Breite	Frame Color Code	Cladding Material
10630-043	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Stahl
10630-044	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Stahl

Table 2/3

Katalognummer	Tiefe	Cladding Color	Cladding Color Code	Konform mit	Frame Material	Product Type
---------------	-------	----------------	---------------------	-------------	----------------	--------------

10630-043	800 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3	Stahl	Schrank
10630-044	800 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3	Stahl	Schrank

Table 3/3		
Katalognummer	Protection Rating	Statische Last
10630-043	IP55	1600 kgf
10630-044	IP55	1600 kgf

ADDITIONAL PRODUCT DETAILS

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE