

Varistar CP Steel Door, Plain With 3-Point Locking, IP55

Data Solutions



Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

FEATURES

Steel door with three point locking for IP 55 protection class

Lever handle with built-in push button

Opening angle 180°

SPECIFICATIONS

Locking Type:	3-Point Locking
Product Type:	Cabinet Door
Protection Rating:	IP55
Material:	Steel

Table 1/2

Catalog Number	Rack Height	Height	Width	Package Quantity	Color	Color Code
21630-171	47U	2200mm	800mm	1	Black Grey	RAL 7021
21630-210	24U	1200mm	600mm	1	Black Grey	RAL 7021
21630-211	29U	1400mm	600mm	1	Black Grey	RAL 7021

CatalogNumber	Rack Height	Height	Width	Package Quantity	Color	Color Code
21630-212	33U	1600mm	600mm	1	Black Grey	RAL 7021
21630-213	38U	1800mm	600mm	1	Black Grey	RAL 7021
21630-214	42U	2000mm	600mm	1	Black Grey	RAL 7021
21630-215	47U	2200mm	600mm	1	Black Grey	RAL 7021
21630-216	24U	1200mm	800mm	1	Black Grey	RAL 7021
21630-217	29U	1400mm	800mm	1	Black Grey	RAL 7021
21630-218	33U	1600mm	800mm	1	Black Grey	RAL 7021
21630-219	38U	1800mm	800mm	1	Black Grey	RAL 7021
21630-220	42U	2000mm	800mm	1	Black Grey	RAL 7021

Table 2/2

Catalog Number	Complies With	Finish	Type	Works With
21630-171	IEC 61587-1	Powder Coated	Steel Door	Varistar CP
21630-210	IEC 61587-1	Powder Coated	Steel Door	Varistar CP
21630-211	IEC 61587-1	Powder Coated	Steel Door	Varistar CP
21630-212	IEC 61587-1	Powder Coated	Steel Door	Varistar CP
21630-213	IEC 61587-1	Powder Coated	Steel Door	Varistar CP
21630-214	IEC 61587-1	Powder Coated	Steel Door	Varistar CP
21630-215	IEC 61587-1	Powder Coated	Steel Door	Varistar CP
21630-216	IEC 61587-1	Powder Coated	Steel Door	Varistar CP

Catalog Number	Complies With	Finish	Type	Works With
21630-217	IEC 61587-1	Powder Coated	Steel Door	Varistar CP
21630-218	IEC 61587-1	Powder Coated	Steel Door	Varistar CP
21630-219	IEC 61587-1	Powder Coated	Steel Door	Varistar CP
21630-220	IEC 61587-1	Powder Coated	Steel Door	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE