

# Varistar CP Side Panel, Screw-Fixed

## Data Solutions

Screw assembly side panel for Varistar CP cabinet.



### FEATURES

Screw fixed, Robust and Single person mountable Side Panel

Side panel without grounding kit

### SPECIFICATIONS

**Product Type:** Cabinet/Rack Panel

Table 1/2

| Catalog Number | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|----------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-043      | 42U         | 2000mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-044      | 42U         | 2000mm | 1100mm | IP20              | 2                | Black Grey |
| 21630-045      | 42U         | 2000mm | 1200mm | IP20              | 2                | Black Grey |
| 21630-046      | 47U         | 2200mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-047      | 47U         | 2200mm | 1100mm | IP20              | 2                | Black Grey |

| CatalogNumber | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|---------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-048     | 47U         | 2200mm | 1200mm | IP20              | 2                | Black Grey |
| 21630-049     | 52U         | 2450mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-050     | 52U         | 2450mm | 1100mm | IP20              | 2                | Black Grey |
| 21630-051     | 52U         | 2450mm | 1200mm | IP20              | 2                | Black Grey |
| 21630-077     | 42U         | 2000mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-078     | 42U         | 2000mm | 1100mm | IP55              | 2                | Black Grey |
| 21630-079     | 42U         | 2000mm | 1200mm | IP55              | 2                | Black Grey |
| 21630-080     | 47U         | 2200mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-081     | 47U         | 2200mm | 1100mm | IP55              | 2                | Black Grey |
| 21630-082     | 47U         | 2200mm | 1200mm | IP55              | 2                | Black Grey |
| 21630-221     | 24U         | 1200mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-222     | 24U         | 1200mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-223     | 24U         | 1200mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-224     | 24U         | 1200mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-225     | 29U         | 1400mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-226     | 29U         | 1400mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-227     | 29U         | 1400mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-228     | 29U         | 1400mm | 1000mm | IP55              | 2                | Black Grey |

| CatalogNumber | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|---------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-229     | 33U         | 1600mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-230     | 33U         | 1600mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-231     | 33U         | 1600mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-232     | 33U         | 1600mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-233     | 38U         | 1800mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-234     | 38U         | 1800mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-235     | 38U         | 1800mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-236     | 38U         | 1800mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-237     | 42U         | 2000mm | 300mm  | IP55              | 2                | Black Grey |
| 21630-238     | 42U         | 2000mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-239     | 42U         | 2000mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-240     | 42U         | 2000mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-241     | 42U         | 2000mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-242     | 42U         | 2000mm | 1100mm | IP55              | 2                | Black Grey |
| 21630-243     | 42U         | 2000mm | 1200mm | IP55              | 2                | Black Grey |
| 21630-244     | 47U         | 2200mm | 300mm  | IP55              | 2                | Black Grey |
| 21630-245     | 47U         | 2200mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-246     | 47U         | 2200mm | 800mm  | IP55              | 2                | Black Grey |

| CatalogNumber | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|---------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-247     | 47U         | 2200mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-248     | 47U         | 2200mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-249     | 47U         | 2200mm | 1100mm | IP55              | 2                | Black Grey |
| 21630-250     | 47U         | 2200mm | 1200mm | IP55              | 2                | Black Grey |
| 21630-261     | 24U         | 1200mm | 600mm  | IP20              | 2                | Black Grey |
| 21630-262     | 24U         | 1200mm | 800mm  | IP20              | 2                | Black Grey |
| 21630-263     | 24U         | 1200mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-264     | 24U         | 1200mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-265     | 29U         | 1400mm | 600mm  | IP20              | 2                | Black Grey |
| 21630-266     | 29U         | 1400mm | 800mm  | IP20              | 2                | Black Grey |
| 21630-267     | 29U         | 1400mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-268     | 29U         | 1400mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-269     | 33U         | 1600mm | 600mm  | IP20              | 2                | Black Grey |
| 21630-270     | 33U         | 1600mm | 800mm  | IP20              | 2                | Black Grey |
| 21630-271     | 33U         | 1600mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-272     | 33U         | 1600mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-273     | 38U         | 1800mm | 600mm  | IP20              | 2                | Black Grey |
| 21630-274     | 38U         | 1800mm | 800mm  | IP20              | 2                | Black Grey |

| CatalogNumber | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|---------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-275     | 38U         | 1800mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-276     | 38U         | 1800mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-277     | 42U         | 2000mm | 300mm  | IP20              | 2                | Black Grey |
| 21630-278     | 42U         | 2000mm | 600mm  | IP20              | 2                | Black Grey |
| 21630-279     | 42U         | 2000mm | 800mm  | IP20              | 2                | Black Grey |
| 21630-280     | 42U         | 2000mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-281     | 47U         | 2200mm | 300mm  | IP20              | 2                | Black Grey |
| 21630-282     | 47U         | 2200mm | 600mm  | IP20              | 2                | Black Grey |
| 21630-283     | 47U         | 2200mm | 800mm  | IP20              | 2                | Black Grey |
| 21630-284     | 47U         | 2200mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-465     | 24U         | 1200mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-466     | 24U         | 1200mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-467     | 29U         | 1400mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-468     | 29U         | 1400mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-469     | 33U         | 1600mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-470     | 33U         | 1600mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-471     | 38U         | 1800mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-472     | 38U         | 1800mm | 800mm  | IP55              | 2                | Black Grey |

| CatalogNumber | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|---------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-473     | 42U         | 2000mm | 300mm  | IP55              | 2                | Black Grey |
| 21630-474     | 42U         | 2000mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-475     | 42U         | 2000mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-476     | 42U         | 2000mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-477     | 47U         | 2200mm | 300mm  | IP55              | 2                | Black Grey |
| 21630-478     | 47U         | 2200mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-479     | 47U         | 2200mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-480     | 47U         | 2200mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-927     | 24U         | 1200mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-928     | 24U         | 1200mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-929     | 29U         | 1400mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-930     | 29U         | 1400mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-931     | 33U         | 1600mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-932     | 33U         | 1600mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-933     | 38U         | 1800mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-934     | 38U         | 1800mm | 1000mm | IP55              | 2                | Black Grey |

Table 2/2

| Catalog Number | Color Code | Finish        | Material | Type                    |
|----------------|------------|---------------|----------|-------------------------|
| 21630-043      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |

| Catalog Number | Color Code | Finish        | Material | Type                    |
|----------------|------------|---------------|----------|-------------------------|
| 21630-044      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-045      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-046      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-047      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-048      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-049      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-050      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-051      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-077      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-078      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-079      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-080      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-081      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-082      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-221      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-222      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-223      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-224      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |

| Catalog Number | Color Code | Finish        | Material | Type                    |
|----------------|------------|---------------|----------|-------------------------|
| 21630-225      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-226      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-227      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-228      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-229      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-230      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-231      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-232      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-233      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-234      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-235      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-236      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-237      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-238      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-239      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-240      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-241      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-242      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |



| Catalog Number | Color Code | Finish        | Material | Type                    |
|----------------|------------|---------------|----------|-------------------------|
| 21630-243      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-244      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-245      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-246      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-247      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-248      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-249      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-250      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-261      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-262      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-263      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-264      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-265      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-266      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-267      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-268      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-269      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-270      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |

| Catalog Number | Color Code | Finish        | Material | Type                    |
|----------------|------------|---------------|----------|-------------------------|
| 21630-271      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-272      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-273      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-274      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-275      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-276      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-277      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-278      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-279      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-280      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-281      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-282      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-283      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-284      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-465      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-466      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-467      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-468      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |

| Catalog Number | Color Code | Finish        | Material | Type                    |
|----------------|------------|---------------|----------|-------------------------|
| 21630-469      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-470      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-471      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-472      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-473      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-474      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-475      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-476      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-477      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-478      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-479      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-480      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-927      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-928      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-929      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-930      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-931      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-932      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |

| Catalog Number | Color Code | Finish        | Material | Type                    |
|----------------|------------|---------------|----------|-------------------------|
| 21630-933      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-934      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |

### ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE