

Earthing and Neutral Busbar with Green/Yellow DIN Rail Clip



Earthing and Neutral Busbars with Green/Yellow DIN Rail Clips are used to connect multiple earthing conductors within a panel and can be used in a variety of different applications including switchgear and control equipment, electrical equipment, wind and solar power generation and in data centers.

CERTIFICATIONS



FEATURES

Use to connect several earthing conductors

Easy for the installer to add connections

Chamfered holes allow for easy connections

Rigid bar

Quick and easy installation on DIN rail

Halogen free

RoHS compliant

SPECIFICATIONS

Material: Brass;Polyethylene

Catalog Number	EB7GYSUP	EB12GYSUP	EB15GYSUP
Article Number	568678	568679	568680

Catalog Number	EB7GYSUP	EB12GYSUP	EB15GYSUP
Number of Connections	7	12	15
Conductor Size, IEC	(1) 6 - 25 mm ² Stranded (6) 1.5 - 16 mm ² Stranded	(1) 6 - 25 mm ² Stranded (11) 1.5 - 16 mm ² Stranded	(1) 6 - 25 mm ² Stranded (14) 1.5 - 16 mm ² Stranded
Max Current Rating	40A	40A	40A
Cross Section	63mm ²	63mm ²	63mm ²
Depth (D)	7mm	7mm	7mm
Height (H)	9 mm	9 mm	9 mm
Width (W)	57 mm	92 mm	113 mm
Hole Size 1 (HS1)	6.5 mm	6.5 mm	6.5 mm
Hole Size 2 (HS2)	5.5 mm	5.5 mm	5.5 mm
Thread Size (TS)	M5	M5	M5
Torque (TQ)	2 N·m	2 N·m	2 N·m
Unit Weight	0.03 kg	0.05 kg	0.06 kg
Complies With	IEC® 60998-2-1	IEC® 60998-2-1	IEC® 60998-2-1

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE