

Novastar Perforated Steel Door

Power Utilities



Perforated doors allow 60 % ventilation thus allowing better passive cooling. Novastar perforated doors come with 180° opening angle and aesthetic looks.

CERTIFICATIONS



FEATURES

Can be mounted at front and rear

Perforated (60 % ventilation opening)

Opening angle 180°

Lock with key (2233X)

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Height	Width	Color	Color Code	Product Type
25230-081	6 U	288.4 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-081	6 U	288.4 mm	553 mm	Light Grey	RAL 7035	Cabinet Door

CatalogNumber	Rack Height	Height	Width	Color	Color Code	Product Type
25230-082	9 U	421.75 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-082	9 U	421.75 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-083	12 U	555.1 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-083	12 U	555.1 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-084	16 U	732.9 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-084	16 U	732.9 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-085	20 U	910.7 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-085	20 U	910.7 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-086	25 U	1132.95 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-086	25 U	1132.95 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-091	29 U	1310.75 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-091	29 U	1310.75 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-087	34 U	1533 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-087	34 U	1533 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-088	38 U	1710.8 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-088	38 U	1710.8 mm	553 mm	Light Grey	RAL 7035	Cabinet Door
25230-089	43 U	1933.05 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-089	43 U	1933.05 mm	553 mm	Light Grey	RAL 7035	Cabinet Door

CatalogNumber	Rack Height	Height	Width	Color	Color Code	Product Type
25230-090	47 U	2110.85 mm	553 mm	Black Grey	RAL 7021	Cabinet Door
26230-090	47 U	2110.85 mm	553 mm	Light Grey	RAL 7035	Cabinet Door

Table 2/2

Catalog Number	Type
25230-081	Steel Door, Perforated
26230-081	Steel Door, Perforated
25230-082	Steel Door, Perforated
26230-082	Steel Door, Perforated
25230-083	Steel Door, Perforated
26230-083	Steel Door, Perforated
25230-084	Steel Door, Perforated
26230-084	Steel Door, Perforated
25230-085	Steel Door, Perforated
26230-085	Steel Door, Perforated
25230-086	Steel Door, Perforated
26230-086	Steel Door, Perforated
25230-091	Steel Door, Perforated
26230-091	Steel Door, Perforated
25230-087	Steel Door, Perforated

Catalog Number	Type
26230-087	Steel Door, Perforated
25230-088	Steel Door, Perforated
26230-088	Steel Door, Perforated
25230-089	Steel Door, Perforated
26230-089	Steel Door, Perforated
25230-090	Steel Door, Perforated
26230-090	Steel Door, Perforated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE