

Novastar Frame, Universal Heavy-Duty

Power Utilities



Asthetic aluminum extruded frame with 400 kg static load capacity. 19" upright built into the frame.

CERTIFICATIONS



FEATURES

Novastar Frame, Universal Heavy-Duty

Aluminium profile, RAL 7021, including grounding

Static load-carrying capacity 400 kg

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Height	Width	Depth	Color	Color Code
----------------	-------------	--------	-------	-------	-------	------------

28230-057	12 U	589 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-058	12 U	589 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-059	12 U	589 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-107	12 U	589 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-108	12 U	589 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-109	16 U	767 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-110	16 U	767 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-111	16 U	767 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-112	16 U	767 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-113	16 U	767 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-114	20 U	945 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-115	20 U	945 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-116	20 U	945 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-117	20 U	945 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-118	20 U	945 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-119	25 U	1167 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-167	25 U	1167 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-168	25 U	1167 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-169	25 U	1167 mm	553 mm	900 mm	Black Grey	RAL 7021

28230-170	25 U	1167 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-171	34 U	1567 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-172	34 U	1567 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-173	34 U	1567 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-174	34 U	1567 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-175	34 U	1567 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-176	38 U	1745 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-177	38 U	1745 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-178	38 U	1745 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-179	38 U	1745 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-180	38 U	1745 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-181	43 U	1967 mm	553 mm	500 mm	Black Grey	RAL 7021
28230-182	43 U	1967 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-183	43 U	1967 mm	553 mm	800 mm	Black Grey	RAL 7021
28230-184	43 U	1967 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-185	43 U	1967 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-052	47 U	2145 mm	553 mm	900 mm	Black Grey	RAL 7021
28230-053	47 U	2145 mm	553 mm	1000 mm	Black Grey	RAL 7021
28230-186	47 U	2145 mm	553 mm	500 mm	Black Grey	RAL 7021

28230-187	47 U	2145 mm	553 mm	600 mm	Black Grey	RAL 7021
28230-188	47 U	2145 mm	553 mm	800 mm	Black Grey	RAL 7021

Table 2/2

Catalog Number	Frame Material	Material	Product Type	Static Load	Type
28230-057	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-058	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-059	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-107	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-108	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-109	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-110	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-111	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-112	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-113	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-114	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-115	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-116	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-117	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-118	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-119	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal

Catalog Number	Frame Material	Material	Product Type	Static Load	Type
28230-167	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-168	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-169	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-170	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-171	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-172	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-173	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-174	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-175	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-176	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-177	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-178	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-179	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-180	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-181	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-182	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-183	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-184	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal

Catalog Number	Frame Material	Material	Product Type	Static Load	Type
28230-185	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-052	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-053	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-186	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-187	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal
28230-188	Aluminum	Aluminum	Cabinet/Rack Frame	400 kgf	Universal

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE