


# Varistar CP 19" Swing Frame Trim



Varistar CP swing frame provides optimum space usage inside the rack. The swing frames come with handles.

## FEATURES

Includes handle and cut-out for cable eyes

To cover the gap between swing frame and cabinet upright for 800 mm wide cabinets

Maximum swing bracket: 120 or 160

For swing frame with load-carrying capacity 150 kg, a stop is recommended for security reasons

Locking no. 333

Spare key for DIN semi-profile cylinder

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Frame

**Material:** Steel

**Works With:** Varistar CP

Table 1/2

| Catalog Number | Rack Height | Design Feature | Package Quantity | Color      | Color Code | Finish        |
|----------------|-------------|----------------|------------------|------------|------------|---------------|
| 21630-746      | 24U         | Asymmetrical   | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-748      | 42U         | Asymmetrical   | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-747      | 33U         | Asymmetrical   | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-751      | 42U         | Symmetrical    | 2                | Black Grey | RAL 7021   | Powder Coated |

| CatalogNumber | Rack Height | Design Feature | Package Quantity | Color      | Color Code | Finish        |
|---------------|-------------|----------------|------------------|------------|------------|---------------|
| 21630-750     | 33U         | Symmetrical    | 2                | Black Grey | RAL 7021   | Powder Coated |
| 21630-749     | 24U         | Symmetrical    | 2                | Black Grey | RAL 7021   | Powder Coated |

Table 2/2

| Catalog Number | Protection Rating | Type  | Quick Ship |
|----------------|-------------------|-------|------------|
| 21630-746      | IP20              | Swing | No         |
| 21630-748      | IP20              | Swing | No         |
| 21630-747      | IP20              | Swing | No         |
| 21630-751      | IP20              | Swing | No         |
| 21630-750      | IP20              | Swing | No         |
| 21630-749      | IP20              | Swing | No         |

## ADDITIONAL PRODUCT DETAILS

Varistar CP swing frame provides optimum space usage inside the rack. The swing frames come with handles.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**