

Varistar CP Cabinet Frame, Seismic

Power Utilities

Welded, steel enclosure engineered specifically to protect equipment in areas with seismic activity and satisfy Bellcore Zore 4 requirements.

FEATURES

St, 1.5 mm, zinc-plated, finish: powder-coated

Earthquake resistance to Bellcore Zone 4

Welded seismic frame with strengthening brackets, RAL 7021

Dynamic load-carrying capacity 250 kg to IEC 61587-2

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Height	Width	Depth	Shock and Vibration Tolerance	Color
20630-358	33 U	1600 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-359	33 U	1600 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-360	33 U	1600 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-361	33 U	1600 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-362	38 U	1800 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-363	38 U	1800 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-364	38 U	1800 mm	800 mm	600 mm	5 g (force)	Black Grey

CatalogNumber	Rack Height	Height	Width	Depth	Shock and Vibration Tolerance	Color
20630-365	38 U	1800 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-366	42 U	2000 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-367	42 U	2000 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-368	42 U	2000 mm	600 mm	1000 mm	5 g (force)	Black Grey
20630-369	42 U	2000 mm	600 mm	1200 mm	5 g (force)	Black Grey
20630-370	42 U	2000 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-371	42 U	2000 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-372	42 U	2000 mm	800 mm	1000 mm	5 g (force)	Black Grey
20630-373	42 U	2000 mm	800 mm	1200 mm	5 g (force)	Black Grey
20630-374	47 U	2200 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-375	47 U	2200 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-376	47 U	2200 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-377	47 U	2200 mm	800 mm	800 mm	5 g (force)	Black Grey

Table 2/3

Catalog Number	Color Code	Complies With	Frame Material	Material	Product Type	Static Load
20630-358	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-359	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-360	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf

CatalogNumber	Color Code	Complies With	Frame Material	Material	Product Type	Static Load
20630-361	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-362	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-363	RAL 7021	IEC 61587-1, IEC 61587-2	Steel		Cabinet/Rack Frame	1600 kgf
20630-364	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-365	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-366	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-367	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-368	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-369	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-370	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-371	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-372	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-373	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-374	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-375	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-376	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf
20630-377	RAL 7021	IEC 61587-1, IEC 61587-2	Steel	Steel	Cabinet/Rack Frame	1600 kgf

Table 3/3

Catalog Number	Type	Works With
----------------	------	------------

20630-358	Seismic	Varistar CP
20630-359	Seismic	Varistar CP
20630-360	Seismic	Varistar CP
20630-361	Seismic	Varistar CP
20630-362	Seismic	Varistar CP
20630-363	Seismic	Varistar CP
20630-364	Seismic	Varistar CP
20630-365	Seismic	Varistar CP
20630-366	Seismic	Varistar CP
20630-367	Seismic	Varistar CP
20630-368	Seismic	Varistar CP
20630-369	Seismic	Varistar CP
20630-370	Seismic	Varistar CP
20630-371	Seismic	Varistar CP
20630-372	Seismic	Varistar CP
20630-373	Seismic	Varistar CP
20630-374	Seismic	Varistar CP
20630-375	Seismic	Varistar CP
20630-376	Seismic	Varistar CP

20630-377	Seismic	Varistar CP
-----------	---------	-------------

ADDITIONAL PRODUCT DETAILS

Please order attachments and components separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE