

Insulated Mounting Panel, AMI



This is an easy to machine mounting plate that will prevent undesired contact between electrical components and the enclosure.

FEATURES

Description: Insulated mounting plate for wall mounted enclosures. By using the AMG accessory, the mounting plate position can be adjusted to any depth. This accessory is not suitable for the AFS range of enclosures, please refer to the replacement and spare parts catalogue.

Material: Bakelite.

Pack quantity: 1 piece.

SPECIFICATIONS

Thickness: 4mm
Material: Bakelite
Color: Black
Finish: Smooth

Table 1/1

Catalog Number	Height	Width	Depth	Panel Size	Enclosure Material	Quick Ship
AMI02020	200mm	200mm	4mm	170 x 150mm	Mild Steel	No
AMI02520	250mm	200mm	4mm	220 x 150mm	Mild Steel	No
AMI02525	250mm	250mm	4mm	220 x 200mm	Mild Steel	No
AMI03025	300mm	250mm	4mm	270 x 200mm	Mild Steel	No
AMI03030	300mm	300mm	4mm	270 x 250mm	Mild Steel	No
AMI03040	300mm	400mm	4mm	270 x 350mm	Mild Steel	No
AMI03525	350mm	250mm	4mm	320 x 200mm	Mild Steel	No
AMI04030	400mm	300mm	4mm	370 x 250mm	Mild Steel	No
AMI04040	400mm	400mm	4mm	370 x 350mm	Mild Steel	No
AMI04050	400mm	500mm	4mm	370 x 450mm	Mild Steel	No
AMI04060	400mm	600mm	4mm	370 x 550mm	Mild Steel	No
AMI05030	500mm	300mm	4mm	470 x 250mm	Mild Steel	No
AMI05040	500mm	400mm	4mm	470 x 350mm	Mild Steel	No
AMI05050	500mm	500mm	4mm	470 x 450mm	Mild Steel	No
AMI06040	600mm	400mm	4mm	570 x 350mm	Mild Steel	No
AMI06050	600mm	500mm	4mm	570 x 450mm	Mild Steel	No

Catalog Number	Height	Width	Depth	Panel Size	EnclosureMaterial	Quick Ship
AMI06060	600mm	600mm	4mm	570 x 550mm	Mild Steel	No
AMI06080	600mm	800mm	4mm	570 x 750mm	Mild Steel	No
AMI07050	700mm	500mm	4mm	670 x 450mm	Mild Steel	No
AMI08040	800mm	400mm	4mm	770 x 350mm	Mild Steel	No
AMI08060	800mm	600mm	4mm	770 x 550mm	Mild Steel	No
AMI08080	800mm	800mm	4mm	770 x 750mm	Mild Steel	No
AMI10060	1000mm	600mm	4mm	970 x 550mm	Mild Steel	No
AMI10080	1000mm	800mm	4mm	970 x 750mm	Mild Steel	No
AMI12060	1200mm	600mm	4mm	1170 x 550mm	Mild Steel	No
AMI12080	1200mm	800mm	4mm	1170 x 750mm	Mild Steel	No

ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE