

Ventilated Bottom Plate, CVB



Can be used in combination with a ventilated plinth PV. 33% ventilated.

FEATURES

Description: Can be used in combination with a ventilated plinth PV. 33% ventilated.

Material: 1.5 mm perforated zinc plated steel.

Pack quantity: 3 pieces, 4 pieces for D>600mm, with mounting material.

Mounting requirements: Use in combination with ventilated plinths PV.

SPECIFICATIONS

Thickness: 1.5mm
Finish: Galvanized
Material: Mild Steel

Table 1/1

Catalog Number	Height	Width	Depth	Enclosure Material	Product Family	Weight
CVB0604	23mm	600mm	400mm	Mild Steel, Galvanized Steel	Free-Standing	
CVB0605	23mm	600mm	500mm	Mild Steel, Galvanized Steel	Free-Standing	
CVB0606	23mm	600mm	600mm	Mild Steel, Galvanized Steel	Free-Standing	2.5kg
CVB0608	23mm	600mm	800mm	Mild Steel, Galvanized Steel	Free-Standing	2.9kg
CVB0804	23mm	800mm	400mm	Mild Steel, Galvanized Steel	Free-Standing	
CVB0805	23mm	800mm	500mm	Mild Steel, Galvanized Steel	Free-Standing	
CVB0806	23mm	800mm	600mm	Mild Steel, Galvanized Steel	Free-Standing	3kg
CVB0808	23mm	800mm	800mm	Mild Steel, Galvanized Steel	Free-Standing	4.4kg
CVB1004	23mm	1000mm	400mm	Mild Steel, Galvanized Steel	Free-Standing	
CVB1005	23mm	1000mm	500mm	Mild Steel, Galvanized Steel	Free-Standing	
CVB1006	23mm	1000mm	600mm	Mild Steel, Galvanized Steel	Free-Standing	
CVB1008	23mm	1000mm	800mm	Mild Steel, Galvanized Steel	Free-Standing	
CVB1206	23mm	1200mm	600mm	Mild Steel, Galvanized Steel	Free-Standing	4.5kg
CVB1208	23mm	1200mm	800mm	Mild Steel, Galvanized Steel	Free-Standing	6.3kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE