

Ventilation Roofs, CVR

The ventilation roof plate provides cost effective natural ventilation while keeping insects and dust out.



FEATURES

Description: Raised roof with 2.5 mm ventilation slots and filter material.

Material: 1.5 mm steel plate. Filter material: EU 4 according to DIN 24185.

Finish: RAL 7035 structured powder coating.

Temperature resistance: 100 °C.

Protection: Complies with IP 31, TYPE 1.

Pack quantity: 1 piece with mounting brackets and ventilation filter.

Note: Increases the enclosure height by 40 mm.

SPECIFICATIONS

Thickness: 1.5mm
Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1						
Catalog Number	Height	Width	Depth	Product Family	Enclosure Material	Quick Ship
CVR0505R5	58mm	500mm	500mm	Free-Standing	Mild Steel	No
CVR0603R5	58mm	600mm	300mm	Free-Standing	Mild Steel	No
CVR0604R5	58mm	600mm	400mm	Free-Standing	Mild Steel	No
CVR0605R5	58mm	600mm	500mm	Free-Standing	Mild Steel	No
CVR0606R5	58mm	600mm	600mm	Free-Standing	Mild Steel	No
CVR0608R5	58mm	600mm	800mm	Free-Standing	Mild Steel	No
CVR0803R5	58mm	800mm	300mm	Free-Standing	Mild Steel	No
CVR0804R5	58mm	800mm	400mm	Free-Standing	Mild Steel	No
CVR0805R5	58mm	800mm	500mm	Free-Standing	Mild Steel	No
CVR0806R5	58mm	800mm	600mm	Free-Standing	Mild Steel	No
CVR0808R5	58mm	800mm	800mm	Free-Standing	Mild Steel	No
CVR0809R5	58mm	800mm	900mm	Free-Standing	Mild Steel	No
CVR1003R5	58mm	1000mm	300mm	Free-Standing	Mild Steel	No
CVR1004R5	58mm	1000mm	400mm	Free-Standing	Mild Steel	No
CVR1005R5	58mm	1000mm	500mm	Free-Standing	Mild Steel	No
CVR1006R5	58mm	1000mm	600mm	Free-Standing	Mild Steel	No

Catalog Number	Height	Width	Depth	Product Family	EnclosureMaterial	Quick Ship
CVR1008R5	58mm	1000mm	800mm	Free-Standing	Mild Steel	No
CVR1203R5	58mm	1200mm	300mm	Free-Standing	Mild Steel	No
CVR1204R5	58mm	1200mm	400mm	Free-Standing	Mild Steel	No
CVR1205R5	58mm	1200mm	500mm	Free-Standing	Mild Steel	No
CVR1206R5	58mm	1200mm	600mm	Free-Standing	Mild Steel	No
CVR1208R5	58mm	1200mm	800mm	Free-Standing	Mild Steel	No
CVR1604R5	58mm	1600mm	400mm	Free-Standing	Mild Steel	No
CVR1605R5	58mm	1600mm	500mm	Free-Standing	Mild Steel	No
CVR1606R5	58mm	1600mm	600mm	Free-Standing	Mild Steel	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE