

Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 84 HP

CATALOG NUMBER

34566-284



Combinations of horizontal rails and side panels

"+" = can be combined, "-" = combination not recommended

Support 2 P		-	-	-	side rail 2 supported
Support 2 S		+	side rail 2 P (fixed) side rail 2 S (fixed)	side rail 2 S (fixed) side rail 2 S (fixed) side rail 2 S (fixed)	+
Support 1		side rail 2 P (fixed)	side rail 2 P (fixed)	-	-
Structural rail		+	+	+	+
Side panel		100% +	flexible +	strong 2 P	Support 2 P


[Go from start](#)

The rugged horizontal rail type can handle shock and vibration up to 25 g.

CERTIFICATIONS



FEATURES

Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

PRODUCT ATTRIBUTES

Rack Width: 84HP

Package Quantity: 1

Finish: Anodized

Length: 431.8mm

Material: Aluminum

Product Family: EuropacPRO

Product Type: Horizontal Rail

Type: Rugged, KD

Works With: Subracks

Gross Weight: 0.26kg

ADDITIONAL PRODUCT DETAILS

Without M4 thread to front, without printing and without notch for 19" bracket.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE