

Horizontal Pouring Basin, Side Fill



Side fill horizontal pouring basins are used when interferences of the structure will not allow top filling of the sleeve.

FEATURES

Made from heat-resistant graphite

Durable, re-usable and long lasting

Designed for use with T-Series and B-Series horizontal side fill sleeves

SPECIFICATIONS

Material: Graphite

Table 1/1									
Catalog Number	Diameter (Ø)	Length 1 (L1)	Length 2 (L2)	Width (W)	Height 1 (H1)	Height 2 (H2)			
RBWS1547F	64 mm	140 mm	22 mm	76 mm	137mm	67mm			
RBWS1547J	76 mm	140 mm	22 mm	76 mm	137mm	67mm			
RBWS1547E	57 mm	140 mm	22 mm	76 mm	137mm	67mm			
RBWS1547M	95 mm	140 mm	22 mm	76 mm	137mm	67mm			
RBWS1547C	48 mm	140 mm	22 mm	76 mm	137mm	67mm			
RBWS1547D	54 mm	140 mm	22 mm	76 mm	137mm	67mm			

CatalogNumber	Diameter (Ø)	Length 1 (L1)	Length 2 (L2)	Width (W)	Height 1 (H1)	Height 2 (H2)
RBWS1547X	38 mm	140 mm	22 mm	76 mm	137mm	67mm


ADDITIONAL PRODUCT DETAILS

RBWS1547 pouring basins require one RBW332 pouring basin frame (sold separately).

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System Instruction Manual.

Sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

©2025 nVent, All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE