

Mounting Plate for 19" Case and Subrack

Power Utilities



Mounting plate for heavy components or proprietary electronic assemblies. Suitable for RatiopacPRO/-AIR, CompacPRO and EuropacPRO.

Guide rails Type 4,4" and type strengthened cannot be used in combination with a mounting plate. Top / bottom cover which will be inserted into the groove of the light (type L) horizontal rails cannot be used in combination with a mounting plate.

CERTIFICATIONS



FEATURES

For assembly of heavy components

Mounting plate, full width: The mounting plate is as wide as the subrack/system case and is fixed to the side panels

Mounting plate, partial width: The partial width mounting plate fixed to the side panel by means of an assembly strip

The chassis plate can't be combined with EMC top- / bottom covers

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Width	Package Quantity	Depth	Material	Product Family	Product Type
34562-752	84 HP	1	172.5 mm	Aluminum	EuropacPRO, CompacPRO, RatiopacPRO, PropacPRO	Mounting Plate

CatalogNumber	Rack Width	Package Quantity	Depth	Material	Product Family	Product Type
34562-756	84 HP	1	232.5 mm	Aluminum	EuropacPRO, RatiopacPRO, CompacPRO	Mounting Plate
34562-760	84 HP	1	292.5 mm	Aluminum	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	Mounting Plate
34562-748	84 HP	1	112.5 mm	Aluminum	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	Mounting Plate
34562-870	84 HP	1	352.5 mm	Aluminum	EuropacPRO	Mounting Plate
34562-871	84 HP	1	412.5 mm	Aluminum	EuropacPRO	Mounting Plate
34562-745	28 HP	1	112.5 mm	Aluminum	EuropacPRO, RatiopacPRO, CompacPRO	Mounting Plate
34562-746	42 HP	1	112.5 mm	Aluminum	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	Mounting Plate
34562-747	63 HP	1	112.5 mm	Aluminum	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	Mounting Plate
34562-749	28 HP	1	172.5 mm	Aluminum	EuropacPRO, RatiopacPRO, CompacPRO	Mounting Plate
34562-750	42 HP	1	172.5 mm	Aluminum	EuropacPRO, CompacPRO, RatiopacPRO, PropacPRO	Mounting Plate
34562-751	63 HP	1	172.5 mm	Aluminum	EuropacPRO, RatiopacPRO, CompacPRO, PropacPRO	Mounting Plate
34562-753	28 HP	1	232.5 mm	Aluminum	EuropacPRO, RatiopacPRO, CompacPRO	Mounting Plate
34562-754	42 HP	1	232.5 mm	Aluminum	EuropacPRO, RatiopacPRO, CompacPRO	Mounting Plate

CatalogNumber	Rack Width	Package Quantity	Depth	Material	Product Family	Product Type
34562-755	63 HP	1	232.5 mm	Aluminum	EuropacPRO, RatiopacPRO, CompacPRO	Mounting Plate
34562-757	28 HP	1	292.2 mm	Aluminum	EuropacPRO, RatiopacPRO, CompacPRO	Mounting Plate
34562-758	42 HP	1	292.2 mm	Aluminum	EuropacPRO, RatiopacPRO, CompacPRO	Mounting Plate
34562-759	63 HP	1	292.2 mm	Aluminum	EuropacPRO, RatiopacPRO, CompacPRO	Mounting Plate

Table 2/2

Catalog Number	Width	Works With	Certifications
34562-752	431.35 mm	Subracks	RoHS
34562-756	431.35 mm	Subracks	RoHS
34562-760	431.35 mm	Subracks	RoHS
34562-748	324.67 mm	Subracks	RoHS
34562-870	431.35 mm	Subracks	
34562-871	431.35 mm	Subracks	
34562-745	146.88 mm	Subracks	RoHS
34562-746	217.99 mm	Subracks	RoHS
34562-747	324.67 mm	Subracks	RoHS
34562-749	146.88 mm	Subracks	RoHS
34562-750	217.99 mm	Subracks	RoHS
34562-751	324.67 mm	Subracks	RoHS

Catalog Number	Width	Works With	Certifications
34562-753	146.88 mm	Subracks	RoHS
34562-754	217.99 mm	Subracks	RoHS
34562-755	324.67 mm	Subracks	RoHS
34562-757	146.88 mm	Subracks	RoHS
34562-758	217.99 mm	Subracks	RoHS
34562-759	324.67 mm	Subracks	RoHS

ADDITIONAL PRODUCT DETAILS

Please order assembly kit for mounting plate separately.

Other versions on request.

Fixing strips required for partial width, please order separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE