

Varistar CP EMC Cabinet, IP 55

Power Utilities



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

FEATURES

Shielding 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3)

Shielding 30 dB at 18 GHz, (tested to EN 61000-5-7) with EN45545 gaskets

Type of protection IP 55

Static load-carrying capacity 1600 kg

Doors with 4-point locking and screw-fixed side panels

Side and rear panels can be installed by one person

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Height	Frame Color	Width	Frame Color Code	Cladding Material
10630-044	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Steel
10630-043	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Steel

Table 2/3

Catalog Number	Depth	Cladding Color	Cladding Color Code	Complies With	Frame Material	Product Type
----------------	-------	----------------	---------------------	---------------	----------------	--------------

10630-044	800 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3	Steel	Cabinet
10630-043	800 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3	Steel	Cabinet

Table 3/3		
Catalog Number	Protection Rating	Static Load
10630-044	IP55	1600 kgf
10630-043	IP55	1600 kgf

ADDITIONAL PRODUCT DETAILS

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE