

QTVR Self-Regulating Heating Cable



nVent RAYCHEM QTVR self-regulating trace heating cables are suitable for freeze protection of large pipes/vessels with high heat loss, and for process temperature maintenance applications without steam-cleaning requirements, up to 225 °F/110 °C. The fluoropolymer outer jacket (-CT) provides high chemical resistance against aggressive organics and corrosives.

FEATURES

Simplified design for hazardous areas: unconditional T4 class

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICATIONS

Max Maintain or Continuous Exposure Temperature, Power On/Off:	110 °C
Max Intermittent Exposure Temperature, Power On/Off:	110 °C
Ground Path Type:	Braid
Outer Jacket Material:	Fluoropolymer
Area Classification:	Non-Hazardous; Hazardous

Table 1/1

Catalog Number	Item Name	Supply Voltage	Nominal Power Output @ 10°C, 230V	Nominal Power Output @ 10°C, 120V
040615-000	15QTVR2-CT	200 – 277 V	51 W/m	
148345-000	15QTVR1-CT	100 – 130 V		52 W/m
259951-000	10QTVR1-CT	100 – 130 V		39 W/m
391991-000	10QTVR2-CT	200 – 277 V	38 W/m	

Catalog Number	Item Name	Supply Voltage	Nominal Power Output @ 10°C, 230V	Nominal Power Output @ 10°C, 120V
498703-000	20QTVR1-CT	100 – 130 V		66 W/m
988967-000	20QTVR2-CT	200 – 277 V	64 W/m	

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT