

XL-Trace Edge Self-Regulating Heating Cable



nVent RAYCHEM XL-Trace Edge self-regulating trace heating cables provide energy efficient and easy to use solutions for pipe freeze protection and flow maintenance of grease waste lines (above and below ground) and fuel lines (above ground).

FEATURES

Simple to design

Easy to install: cut to length, meter marks, fast RayClick cold connection system

Energy efficient and safe: self-regulating cable, advanced energy saving controls, no cable overheating possible, suitable for plastic pipes

Reliable during long life: 10 year extended product warranty available, maintenance free

SPECIFICATIONS

Min Installation Temperature: -18 °C

Ground Path Type: Braid

Table 1/1

Catalog Number	Item Name	Supply Voltage	Outer Jacket Material	Max Circuit Length	Max Continuous Exposure Temperature, Power Off
2000002607	5XLE1-CR	120 V	Modified Polyolefin		85 °C
2000002608	5XLE2-CR	208 – 277 V	Modified Polyolefin	178 m	85 °C
2000002609	8XLE1-CR	120 V	Modified Polyolefin		85 °C
2000002610	8XLE2-CR	208 – 277 V	Modified Polyolefin	138 m	85 °C

Catalog Number	Item Name	Supply Voltage	Outer Jacket Material	Max CircuitLength	Max Continuous Exposure Temperature, Power Off
2000002611	5XLE1-CT	120 V	Fluoropolymer		85 °C
2000002612	5XLE2-CT	208 – 277 V	Fluoropolymer	178 m	85 °C
2000002613	8XLE1-CT	120 V	Fluoropolymer		85 °C
2000002614	8XLE2-CT	208 – 277 V	Fluoropolymer	138 m	85 °C
P000000793	12XLE2-CR	208 – 277 V	Modified Polyolefin	110 m	85 °C
P000000794	12XLE2-CT	208 – 277 V	Fluoropolymer	110 m	85 °C

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT