


Eurorack Slide Rail, 25 kg



Eurorack Slide Rail with 25 kg load capacity for mounting on the cabinet uprights or 19" panel/slide mounts. The slide rail supports shelf of heavy 19" Chassis.

CERTIFICATIONS



FEATURES

St, 1.5 mm, finish AlZn

Static load-carrying capacity 25 kg per pair

Support shelf of heavy 19" chassis

For assembly on the 19" panel/slide mounts

Wide support surface

Can be attached in 1 U increments

SPECIFICATIONS

Static Load: 25kg

Product Type: Slide Rail

Material: Steel

Table 1/1

Catalog Number	Depth	Length	Package Quantity	Finish	Quick Ship
----------------	-------	--------	------------------	--------	------------

22127-094	600mm	420mm	2	Aluminum-Zinc Plated	No
25127-575	800mm	512mm	2	Aluminum-Zinc Plated	No
22127-095	800mm	620mm	2	Aluminum-Zinc Plated	No
22127-096	900mm	717mm	2	Aluminum-Zinc Plated	No
21127-197	600mm	420mm	10	Aluminum-Zinc Plated	No
21127-198	800mm	620mm	10	Aluminum-Zinc Plated	No
21127-199	900mm	720mm	10	Aluminum-Zinc Plated	No

ADDITIONAL PRODUCT DETAILS

Standard distance for servers d = 740 mm. For assembly 4 pieces panel/slide mounts are necessary (please order separately, see panel/slide mount).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE