


# Novastar 19" Panel/Slide Mount

The Novastar 3 U Panel/Slide mount is for the 19" plane for universal upright.



## CERTIFICATIONS



## FEATURES

Panel/slide mount for installing on the universal profile

A 19" plane can be implemented using the panel/slide mount

## SPECIFICATIONS

**Product Type:** Slide Mount

**Material:** Steel

Table 1/2

| Catalog Number | Rack Height | Package Quantity | Color      | Color Code | Finish        | Height |
|----------------|-------------|------------------|------------|------------|---------------|--------|
| 27230-162      | 3U          | 1                | Black Grey | RAL 7021   | Powder Coated | 130mm  |
| 27230-163      | 4U          | 1                | Black Grey | RAL 7021   | Powder Coated | 130mm  |

Table 2/2

| Catalog Number | Package Unit | Quick Ship |
|----------------|--------------|------------|
|----------------|--------------|------------|

|           |      |    |
|-----------|------|----|
| 27230-162 | Pair | No |
| 27230-163 | Pair | No |

## ADDITIONAL PRODUCT DETAILS

Please order cover plate or brush strip separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**